

# Hydrogen Generators

for GC combustion detector applications




The Parker domnick hunter H high purity hydrogen gas generators offer the optimum combination of safe operation, reliability and performance.

Utilising field proven PEM cell technology, hydrogen is produced on demand from deionised water and electricity, at low pressure and with minimal stored volume. Innovative control software allows unrivalled operational safety and reliability.

The H generators ideally supply fuel gas to all known GC combustion detectors used in today's laboratory workflows. Three models operate at flow rates; 160 ml/min, 250 ml/min and 500 ml/min.

Hydrogen generators are available with Remote Networking software. RemoteNet allows up to 27 hydrogen generators to be actively controlled from one central PC, and facilitates true cascading capabilities.



## Contact Information:

**Parker Hannifin Ltd.**  
domnick hunter Industrial Division  
Dukesway, Team Valley Trading Estate  
Gateshead, Tyne and Wear  
England NE11 0PZ

**Tel: +44 (0)191 402 9000**  
**Fax: +44 (0)191 482 6296**  
**Email: [gasgen@parker.com](mailto:gasgen@parker.com)**  
**[www.domnickhunter.com](http://www.domnickhunter.com)**

## Product Features:

- **Eliminate dangerous hydrogen cylinders from the work place**
- **Simple to install and operate**
- **Compact, reliable with minimal maintenance**
- **Produces a continuous supply of 99.9995% pure hydrogen at up to 6.9 bar**
- **2 year standard cell warranty**
- **Optional automatic water fill and remote networking capability**

## Product Selection

Model	Flow Rate		Purity*	Water Consumption (24/7, full flow)	Delivery Pressure		Optional Auto Water Fill (AWF)
	ml/min				bar g	psi g	
20H	160		>99.9995	1.25	0.3-6.89	5-100	YES
40H	250		>99.9995	2	0.3-6.89	5-100	YES
60H	500		>99.9995	4	0.3-6.89	5-100	YES

\*With respect to oxygen

Note: For auto water fill option add suffix AWF ie 20H-AWF

## Technical Data

Ambient Temperature Range	5 - 40°C 41 - 104°F
Water Supply Pressure*	0.1 bar g 1.45 psi g
Water Supply Flow Rate*	1 L/min
Water Quality	Deionised. ASTM II, >1MΩ, <1µs, filtered to <100µm
Supply Voltage Range	90 - 264V 50/60Hz
Port Connections	Hydrogen Outlet Water Drain Water Fill*
	1/8" Compression Fitting Quick Release Push in Fitting Quick Release Push in Fitting

\*With optional AWF

## Weights and Dimensions

Model	Height (H)		Width (W)		Depth (D)		Weight (Empty)		Weight (Full of Water)	
	mm	in	mm	in	mm	in	kg	lb	kg	lb
20H	456	17.9	342	13.5	437	17.2	19	41.9	23	50.7
40H	456	17.9	342	13.5	437	17.2	19	41.9	23	50.7
60H	456	17.9	342	13.5	437	17.2	19	41.9	23	50.7

## Preventative Maintenance

Preventative Maintenance Kit	Part Number	Change Frequency
Replacement desiccant cartridge	604970412	As required*
6 month kit	604970600	6 months
24 month kit	604970532	12 Months

\* 20H Continuous operation approx 6 to 7 months

\* 40H Continuous operation approx 4 to 5 months

\* 60H Continuous operation approx 2 to 3 months

## Optional Extra's

Description	Part Number	Required for
RemoteNet user software	604971510	up to two generators
RemoteNet user add on kit	604971520	each additional generator (604971510 required)